

## Mini Voice Amplifier (Hearing Aid)

### *Low Noise Activation*

**Model No. : VA-3000**

### Slim & Light Voice Amplifier



with mono earphone

- It is useful for people having low hearing ability and when people hear little sound largely.
- It is easy and simple to wear.
- It is safe due to the built-in circuit to prevent howling and circuit to block loud noise.
- It enables people to enjoy large and clear sound in conversation, watching TV, at concert/lecture/church, etc.
- It amplifies the sound 16 times larger.

### Features



with Stereo Earphone

- Easy to wear due to mini size.
- Built-in circuits to prevent howling and to block loud noise.
- Volume control : 10 levels.
- 4 tones setting : low sound emphasis, middle sound emphasis, high sound emphasis, normal
- Battery life time : 24 hours (long time use)
- Battery charging time : 1 hour 30 minutes (quick charging method)
- Battery charging method: by PC USB or AC adaptor(option).
- Remainin battery indicator : 3 levels.
- Battery type : Li-polymer, rechargeable 3.7v/80mA.
- Weight & Dimension : 7.3g / 15(W)X54(L)X12(D)mm.

### How to use

When you press power button long (more than 2 seconds), it is turned on or off.

Volume is controlled by pressing Volume +/- button shortly

Mode setting is changed in order by pressing Volume +/- button long



### Accessory



USB charging cable



Ear hanger



Ear rubber



Streo earphone(option)



Clip(option)